



# KR 180 R3200 PA



## Technical data

Maximum reach	3195 mm
Rated payload	180 kg
Rated supplementary load, rotating column / link arm / arm	0 kg / 0 kg / 50 kg
Rated total load	NaN kg
Pose repeatability (ISO 9283)	± 0.06 mm
Number of axes	5
Mounting position	Floor
Footprint	830 mm x 830 mm
Weight	approx. 1093 kg

#### Axis data

Motion range	
A1	±185 °
A2	-140 ° / -5 °
A3	0 ° / 155 °
A4	-
A5	-
A6	±350 °
Speed with rated payload	
A1	105 °/s
A2	107 °/s
A3	114 °/s
A4	-
A5	173 °/s
A6	242 °/s

### **Operating conditions**

Ambient temperature during oper- 0 °C to 55 °C (273 K to 328 K) ation


### **Protection rating**

Protection rating (IEC 60529)	IP65
Protection rating, robot wrist (IEC	IP65
60529)	

## Controller

Controller	KR C4
------------	-------

### Workspace graphic



### Mounting flange

