

# $\bigcirc$

# KR 10 R900-2



#### **Technical data**

Maximum reach	901 mm
Maximum payload	11.3 kg
Pose repeatability (ISO 9283)	± 0.02 mm
Number of axes	6
Mounting position	Floor;
	Ceiling;
	Wall;
	Desired angle
Footprint	208 mm x 208 mm
Weight	approx. 55 kg

# Axis data

Motion range	
A1	±170 °
A2	-190 ° / 45 °
A3 A4 A5	-120 ° / 156 °
A4	±185 °
A5	±120 °
A6	±350 °

#### **Operating conditions**

Ambient temperature during opera- 0 °C to 45 °C (273 K to 318 K) tion

#### **Protection rating**

Protection rating (IEC 60529)	IP65 / IP67
Protection rating, robot wrist (IEC	IP65 / IP67
60529)	

#### Controller

Controller	KR C5 micro;
	KR C4 compact


## Certificates

#### Cycle time


141 cycles per minute (25 mm / 305 mm / 25 mm, 1 kg)



#### Workspace graphic




### Payload diagram



The KR 10 R900-2 is designed for a rated payload of 5 kg in order to optimize the dynamic performance of the robot. The maximum payload of 11.3 kg applies only if the position of the center of mass is 0 mm and a supplementary load optimized for the load case is mounted. The specific load case must be verified using KUKA.Load or KUKA Compose. For further consultation, please contact KUKA Support.

#### Mounting flange



Details provided about the properties and usability of the products are purely for information purposes and do not constitute a guarantee of these characteristics. The extent of goods delivered and services performed is determined by the subject matter of the specific contract. No liability accepted for errors or omissions. 0000-290-002 / V13.1 / 26.05.2022 / en

KUKA Deutschland GmbH Zugspitzstrasse 140, 86165 Augsburg, Germany. Tel.: +49 821 797-4000, www.kuka.com