



KR 6 R700 HM-SC



Technical data

Maximum reach	706.7 mm
Maximum payload	6 kg
Pose repeatability (ISO 9283)	± 0.03 mm
Number of axes	6
Mounting position	Floor;
	Ceiling;
	Wall;
	Desired angle
Footprint	320 mm x 320 mm
Weight	approx. 60 kg

Axis data

Motion range	
A1	±166 °
A2 A3 A4 A5 A6	-188 ° / 45 °
A3	-115 ° / 144 °
A4	±185 °
A5	±110 °
A6	±350 °

Operating conditions

Ambient temperature during opera-	0 °C to 35 °C (273 K to 308 K)
tion	


Protection rating

Protection rating (IEC 60529)	IP65 / IP67
Protection rating, robot wrist (IEC	IP65 / IP67
60529)	


Controller

Controller	KR C4 compact
Controller	NN C4 COMPact


Cycle time



Workspace graphic



Payload diagram



The KR 6 R700 HM-SC is designed for a rated payload of 3 kg in order to optimize the dynamic performance of the robot. The maximum payload of 6 kg applies only if the position of the center of mass is 0 mm and a supplementary load optimized for the load case is mounted. The specific load case must be verified using KUKA.Load or KUKA Compose. For further consultation, please contact KUKA Support.

Mounting flange

