

\bigcirc

KR 20 R2010 KS-F



Technical data

Maximum reach	2010 mm
Rated payload	20 kg
Maximum payload	23.9 kg
Maximum supplementary load, ro- tating column / link arm / arm	20 kg / 15 kg / 15 kg
Pose repeatability (ISO 9283)	± 0.04 mm
Number of axes	6
Mounting position	Floor
Footprint	440 mm x 370 mm
Weight	approx. 242 kg

Axis data

±125 °
-120 ° / 90 °
-138 ° / 175 °
±350 °
±130 °
±350 °
200 °/s
175 °/s
190 °/s
430 °/s
430 °/s
630 °/s

Operating conditions

Ambient temperature during opera- $\,$ 5 $^{\circ}\text{C}$ to 45 $^{\circ}\text{C}$ (278 K to 318 K) tion


Protection rating

Protection rating (IEC 60529)	IP65
Protection rating, robot wrist (IEC 60529)	IP67


Controller

Controller	KR C5;
Controller	NN 00,
	KR C4

Workspace graphic




Payload diagram



The KR 20 R2010 KS-F is designed for a rated payload of 20 kg in order to optimize the dynamic performance of the robot. The maximum payload of 23.9 kg applies only if the position of the center of mass is 0 mm and a supplementary load optimized for the load case is mounted. The specific load case must be verified using KUKA.Load or KUKA Compose. For further consultation, please contact KUKA Support.

Mounting flange



Details provided about the properties and usability of the products are purely for information purposes and do not constitute a guarantee of these characteristics. The extent of goods delivered and services performed is determined by the subject matter of the specific contract. No liability accepted for errors or omissions. 0000-283-957 / V13.1 / 26.05.2022 / en

KUKA Deutschland GmbH Zugspitzstrasse 140, 86165 Augsburg, Germany. Tel.: +49 821 797-4000, www.kuka.com