



KR 250 R2700-2 C



Technical data

Maximum reach	2671 mm
Rated payload	250 kg
Maximum payload	305 kg
Maximum supplementary load, rotat-	-
ing column / link arm / arm	
Pose repeatability (ISO 9283)	± 0.05 mm
Number of axes	6
Mounting position	Ceiling
Footprint	754 mm x 754 mm
Weight	approx. 1105 kg

Axis data

A1	Motion range	
A3	A1	±185 °
A4		-140 ° / -14 °
A5 ±122.5 ° A6 ±350 ° Speed with rated payload A1 105 °/s A2 107 °/s A3 107 °/s A4 170 °/s A5 129 °/s	A3	-120 ° / 168 °
A6 ±350 ° Speed with rated payload A1 105 °/s A2 107 °/s A3 107 °/s A4 170 °/s A5 129 °/s	A4	±350 °
Speed with rated payload A1 105 °/s A2 107 °/s A3 107 °/s A4 170 °/s A5 129 °/s	A5	±122.5 °
A1 105 °/s A2 107 °/s A3 107 °/s A4 170 °/s A5 129 °/s	A6	±350 °
A2 107 °/s A3 107 °/s A4 170 °/s A5 129 °/s	Speed with rated payload	
A3 107 °/s A4 170 °/s A5 129 °/s	A1	105 °/s
A4 170 °/s A5 129 °/s	A2	107 °/s
A5 129 °/s	A3	107 °/s
	A4	170 °/s
A6 206 %	A5	129 °/s
710 200 /3	A6	206 °/s

Operating conditions

Ambient temperature during opera-	0 °C to 55 °C (273 K to 328 K
tion	

Protection rating

•	
Protection rating (IEC 60529)	IP65
Protection rating, robot wrist (IEC	IP65 / IP67
60529)	


Controller

Controller	KR C5;
	KR C4


Certificates

ESD requirements IEC61340-5-1; ANSI/ESD S20.20

Workspace graphic



Payload diagram



The KR 250 R2700-2 C is designed for a rated payload of 250 kg in order to optimize the dynamic performance of the robot. The maximum payload of 305 kg applies only if the position of the center of mass is 0 mm and a supplementary load optimized for the load case is mounted. The specific load case must be verified using KUKA.Load or KUKA Compose. For further consultation, please contact KUKA Support.

Mounting flange

