



# KR 6 R700 Z200



#### **Technical data**

700 mm
6 kg
± 0.02 mm
4
Floor
262 mm x 190 mm
approx. 21 kg

### Axis data

Motion range	
Motion range, axis 1	±132 °
Motion range, axis 2	±145 °
Motion range, axis 3	-200 mm / 0 mm
Motion range, axis 4	±355 °
Speed with rated payload	
Axis velocity, axis 1	420 °/s
Axis velocity, axis 2	720 °/s
Axis velocity, axis 3	1.1 m/s
Axis velocity, axis 4	2000 °/s

#### **Operating conditions**

Ambient temperature during oper- 5 °C to 40 °C (278 K to 313 K) ation


#### **Protection rating**

Protection rating	(IEC 60529)	IP20


## Controller

KR C5 micro

#### Workspace graphic



#### Payload diagram



The KR 6 R700 Z200 is designed for a rated payload of 3 kg in order to optimize the dynamic performance of the manipulator. With the reduced load center distances, higher loads up to the maximum payload may be used. The specific load case must be verified using KUKA.Load. For further consultation, please contact KUKA Support.

#### Cycle time

157 cycles per minute (25 mm / 305 mm / 25 mm, 1 kg)



KUKA Deutschland GmbH Zugspitzstrasse 140, 86165 Augsburg, Germany. Tel.: +49 821 797-4000, www.kuka.com