



# KR 280 R3080 F



#### Technical data

Maximum reach	3076 mm
Rated payload	280 kg
Maximum payload	356 kg
Maximum supplementary load, rotat-	-
ing column / link arm / arm	
Pose repeatability (ISO 9283)	± 0.08 mm
Number of axes	6
Mounting position	Floor
Footprint	1050 mm x 1050 mm
Weight	approx. 2415 kg

#### Axis data

Motion range	
A1	±185 °
A2	-130 ° / 20 °
A3	-100 ° / 144 °
A4	±350 °
A5	±120 °
A6	±350 °
Speed with rated payload	
A1	100 °/s
A2	90 °/s
A3	90 °/s
A4	120 °/s
A5	110 °/s
A6	160 °/s

### **Operating conditions**

Ambient temperature during opera-	10 °C to 55 °C (283 K to 328 K)
tion	


#### Protection rating

•	
Protection rating (IEC 60529)	IP65
Protection rating, robot wrist (IEC	IP67
60529)	


#### Controller

Controller	KR C5;
	KR C4

## Workspace graphic



### Payload diagram



The KR 280 R3080 F is designed for a rated payload of 280 kg in order to optimize the dynamic performance of the robot. The maximum payload of 356 kg applies only if the position of the center of mass is 0 mm and a supplementary load optimized for the load case is mounted. The specific load case must be verified using KUKA.Load or KUKA Compose. For further consultation, please contact KUKA Support.

# Mounting flange

