



**KR 4 AGILUS** 

New possiblities, shaped from greater functionality.





**Custom-tailored for maximum performance in production.** High performance in any installation position and with minimal space requirements – the KR 4 AGILUS impresses with its compact design, long reach and high precision.

The KR 4 AGILUS combines ultra-compact, interference-free design with optimum performance: with a payload capacity of 4 kilograms and a reach of 600 millimeters, the compact robot performs a wide variety of tasks, such as handling and assembly in the electronics industry or in small automation cells. It works reliably and precisely even with the shortest cycle times.

Multi-functional applicability, flexible positioning and unbeatable reliability – the new KR 4 AGILUS pushes back the boundaries of technical feasibility in small robotics. With a payload of up to 3 kilograms, it impresses with a top cycle time as fast as 0.4 seconds\*. Whether handling, continuous-path motion or working with pinpoint accuracy – the KR 4 AGILUS simplifies the automation of compact and ultra-compact cells. Flexible in installation, highly precise in motion, economical in maintenance.

With just one type of robot, your applications will sustainably reach new levels of performance and efficiency. For maximum performance over the entire temperature range between 0 and 55 °C. Furthermore, the KR 4 AGILUS has an internally-routed media supply for air, power and data, enabling the quick and easy integration of peripheral devices. As a robot of the latest generation, the KR 4 AGILUS operates with the KR C5 micro, incorporating state-of-the-art control technology from KUKA. In order to solve and control tasks more efficiently and intuitively.

**Speed.** Cycle times as fast as 0.4 seconds

**Durability.** Suitable for use in the temperature range from 0 to 55 °C, equipped with protection rating IP 40 and ESD protection

**Precision.** Repeatability of 0.02 millimeters and improved continuous-path accuracy

## Integrated energy supply system.

Compatible with most supply systems  $4 \times 4$  compressed air  $1 \times M12$  8-pin (24 V, 2 A)  $1 \times M12$  8-pin Ethernet (optional)



**Utmost flexibility.** Compact, interference-free design, flexible installation position and various interfaces for peripheral devices.

**ESD protection.** As standard, the robot is protected against uncontrolled electrostatic charging or discharging and is thus equipped for the safe handling of sensitive electronic components.

**Maximum reliability.** Particularly long service life and low servicing and maintenance requirements, e.g. thanks to fewer steps when exchanging cables

**Simple operation.** Control via KR C5 micro and operation via the KUKA smartPAD



Integrated media supply for air, power and data. For minimum disruptive contours and maximum reliability in operation.







Reach 601 mm



**Payload** 4 kg

KR 4 AGILUS	KR 4 R600
Controller	KR C5 micro
Number of axes	6
Payload	4 kg
Reach	601 mm
Pose repeatability	±0.02 mm
Weight	27 kg
Installation position	Floor, ceiling, wall, angle

<sup>\*</sup>Cycle time according to the "Small Adept Cycle" reference standard



wkuka.com/contacts

facebook.com/kukaglobal

youtube.com/kukarobotgroup

twitter.com/kukaglobal

in linkedin.com/company/kukaglobal

Angaben zur Beschaffenheit und Verwendbarkeit der Produkte stellen keine Zusicherung von Eigenschaften dar, sondern dienen lediglich Informationszwecken. Maßgeblich für den Umfang unserer Lieferungen ist der jeweilige Vertragsgegenstand. Technische Daten und Abbildungen sind unverbindlich in Hinblick auf Lieferungen. Änderungen vorbehalten. © 2022 KUKA