



KR 6 R700 Z200-2



Technical data

| Maximum reach | 700 mm |
|-------------------------------|-----------------|
| Maximum payload | 6 kg |
| Pose repeatability (ISO 9283) | ± 0.02 mm |
| Number of axes | 4 |
| Mounting position | Floor |
| Footprint | 262 mm x 190 mm |
| Weight | approx. 22 kg |

Axis data

| Motion range | |
|--------------------------|----------------|
| Motion range, axis 1 | ±132 ° |
| Motion range, axis 2 | ±145 ° |
| Motion range, axis 3 | -200 mm / 0 mm |
| Motion range, axis 4 | ±355 ° |
| Speed with rated payload | |
| Axis velocity, axis 1 | 420 °/s |
| Axis velocity, axis 2 | 720 °/s |
| Axis velocity, axis 3 | 1.1 m/s |
| Axis velocity, axis 4 | 2000 °/s |
| | |

Operating conditions

Ambient temperature during oper- $5~^{\circ}\text{C}$ to 40 $^{\circ}\text{C}$ (278 K to 313 K) ation

Protection rating

| Protection rating (IEC 60529) | IP 20 |
|-------------------------------|-------|


Controller

Controller KR C5 micro


Certificates

ESD requirements IEC61340-5-1; ANSI/ESD S20.20

Workspace graphic



Payload diagram



The KR 6 R700 Z200-2 is designed for a rated payload of 3 kg in order to optimize the dynamic performance of the manipulator. With the reduced load center distances, higher loads up to the maximum payload may be used. The specific load case must be verified using KUKA.Load. For further consultation, please contact KUKA Support.

Cycle time

