



KR 340 R3330



Technical data

Maximum reach	3326 mm
Rated payload	340 kg
Maximum payload	418 kg
Maximum supplementary load, rotat-	-
ing column / link arm / arm	
Pose repeatability (ISO 9283)	± 0.08 mm
Number of axes	6
Mounting position	Floor
Footprint	1050 mm x 1050 mm
Weight	approx. 2421 kg

Axis data

A1	Motion range	
A3	A1	±185 °
A4 ±350 ° A5 ±120 ° A6 ±350 ° Speed with rated payload A1 90 °/s A2 80 °/s A3 75 °/s A4 90 °/s		-130 ° / 20 °
A5	A3	-100 ° / 144 °
A6 ±350 ° Speed with rated payload A1 90 °/s A2 80 °/s A3 75 °/s A4 90 °/s		±350 °
Speed with rated payload A1 90 °/s A2 80 °/s A3 75 °/s A4 90 °/s	A5	±120 °
A1 90 °/s A2 80 °/s A3 75 °/s A4 90 °/s	A6	±350 °
A2 80 °/s A3 75 °/s A4 90 °/s	Speed with rated payload	
A3 75 °/s A4 90 °/s	A1	90 °/s
A4 90 °/s		80 °/s
	A3	75 °/s
A5 83 °/s	A4	90 °/s
	A5	83 °/s
A6 130 °/s	A6	130 °/s

Operating conditions

Ambient temperature during opera-	10 °C to 55 °C (283 K to 328 K)
tion	


Protection rating

•	
Protection rating (IEC 60529)	IP65
Protection rating, robot wrist (IEC	IP65
60529)	


Controller

Controller	KR C5;
	KR C4

Workspace graphic



Payload diagram



The KR 340 R3330 is designed for a rated payload of 340 kg in order to optimize the dynamic performance of the robot. The maximum payload of 418 kg applies only if the position of the center of mass is 0 mm and a supplementary load optimized for the load case is mounted. The specific load case must be verified using KUKA.Load or KUKA Compose. For further consultation, please contact KUKA Support.

Mounting flange

