



KR 500 R2830 C-F



Technical data

Maximum reach	2485 mm
Rated payload	500 kg
Maximum payload	611 kg
Maximum supplementary load, rotat-	-
ing column / link arm / arm	
Pose repeatability (ISO 9283)	± 0.08 mm
Number of axes	6
Mounting position	Ceiling
Footprint	1050 mm x 1050 mm
Weight	approx. 2385 kg

Axis data

±185 °
-130 ° / 20 °
-100 ° / 144 °
±350 °
±120 °
±350 °
90 °/s
80 °/s
75 °/s
90 °/s
83 °/s
130 °/s

Operating conditions

Ambient temperature during opera-	10 °C to 55 °C (283 K to 328 K)
tion	


Protection rating

o o	
Protection rating (IEC 60529)	IP65
Protection rating, robot wrist (IEC	IP67
60529)	


Controller

Controller	KR C5;
	KR C4

Workspace graphic



Payload diagram



The KR 500 R2830 C-F is designed for a rated payload of 500 kg in order to optimize the dynamic performance of the robot. The maximum payload of 611 kg applies only if the position of the center of mass is 0 mm and a supplementary load optimized for the load case is mounted. The specific load case must be verified using KUKA.Load or KUKA Compose. For further consultation, please contact KUKA Support.

Mounting flange

